

# Clearz and Spheres Information

## Standard (18") Clearz and Spheres

Inflated Size*	Volume	Lift Ability**	Flying Time***
18"/45.5cm	1.77ft <sup>3</sup> /0.050m <sup>3</sup>	1.23oz/35g	+/- 3 days
19"/48cm	2.08ft <sup>3</sup> /0.059m <sup>3</sup>	1.66oz/47g	+/- 4 days
20"/50.5cm	2.42ft <sup>3</sup> /0.069m <sup>3</sup>	2.05oz/58g	+/- 5 days
21"/53cm	2.81ft <sup>3</sup> /0.080m <sup>3</sup>	2.47oz/70g	+/- 6 days
22"/55.5cm	3.23ft <sup>3</sup> /0.091m <sup>3</sup>	3.0oz/85g	+/- 7 days

## Clearz Petites

10"/25.5cm	0.30ft <sup>3</sup> /0.008m <sup>3</sup>	0.17oz/4.8g	+/- 24 hours
11"/28cm	0.40ft <sup>3</sup> /0.011m <sup>3</sup>	0.27oz/7.7g	+/- 36 hours
12"/30.5cm	0.52ft <sup>3</sup> /0.015m <sup>3</sup>	0.38oz/10.7g	+/- 48 hours
13"/33cm	0.66ft <sup>3</sup> /0.019m <sup>3</sup>	0.52oz/14.8g	+/- 60 hours
14"/35.5cm	0.83ft <sup>3</sup> /0.024m <sup>3</sup>	0.69oz/19.5g	+/- 72 hours

\*recommended minimum size for helium filling is 18"/45.5cm for Standard Clearz and Spheres and 10"/25.5cm for Clearz Petites to ensure adequate flight time.

When air filling, minimum inflated size is 15"/38cm for Standard Clearz and Spheres and 9"/23cm for Clearz Petites to ensure wrinkle-free seams.

\*\* Measured at 361ft/110m above sea level. Lift ability will decrease with increased altitude. Figures shown are MAXIMUM lift.

\*\*\* Flying time will vary with temperature, altitude, and weight attached to balloon. Figures are approximate.

 @amscanuk  
 @amscanuk  
 @AmscanInternational  
 www.amscan.co.uk

our family of companies



©amscan 2020, ©anagram 2020. All Rights Reserved.

Amscan International Ltd.  
Brudenell Drive, Brinklow  
Milton Keynes, MK10 0DA

 +44 (0)1908 288 500  
 sales@amscan-uk.co.uk

